


UELI – Universal Extendible Label Inspection

Built for your process, validated printer and setup



Ideal for pharmaceutical, medtech and chemical applications, where legibility, quality and documentation are non-negotiable.


Adaptable by design: UELI fits into your environment: a height-adjustable inspection station with matrix camera and illumination and an industrial panel PC running QualiReader inspection software. You intend to retrofit your existing print equipment with a vision inspection or you want to build a compact table-top printing cell and you bring the label printer, with or without a rewinder. UELI verifies pre-printed elements, codes, text, symbols and variable data so that good labels keep moving and bad ones are stopped.

Digital reference, less setup: UELI works with a digital reference either manually imported or directly from your LMS/ERP via Level 3 or Hotfolder. When the LMS/ERP supplies the digital reference with meta data such as field definitions and formats, QualiReader automatically selects the appropriate inspection method and parameters for each relevant print area. If a digital reference is not directly accessible, simply import a picture or PDF to get going quickly. No image acquisition and golden image for teaching, no re-teaching for each change to the artwork needed.

Built for your process: Image capture synchronizes to the printer via I/O, ensuring consistent inspection at speed. Orders and articles are managed on the system and can be operated via touchscreen, order sheet (code scanner) or remotely. Results are stored locally on the IPC and can also be mirrored to your database, LMS or ERP for traceability.

Results you can trust: Legibility of static or variable content is checked with LegibilityCheck; codes are read and compared with order data (and optionally classified with a grading approximation); serialized text fields can be verified with OCR/OCV. Out-map excludes non-relevant areas to keep performance high and false rejects low.

How UELI works (can be adapted to the customer's process)



1. **Import the layout:** Retrieve the digital reference directly from the LMS/ERP via Level 3, or upload a picture/PDF reference manually.
2. **Automatic teach-in:** Based on what is printed, where, and in which format, QualiReader automatically chooses the best inspection method for each print area and sets the image-processing parameters.
3. **Start order and inspect:** The matrix camera and illumination capture each label; printer I/O triggers image capture and controls the feed. If a label is non-OK, the process pauses. The operator removes the faulty label and confirms the action in QualiReader.
4. **Documentation:** All results are stored on the IPC per order/article, including pass/fail status and statistics, and can also be transferred to your IT systems (database, LMS, or ERP).

LegibilityCheck: GMP-grade legibility, by design

LegibilityCheck is a geometry based, layout driven inspection algorithm for static text, logos and artwork designed to test your legibility. Using the digital reference, it decomposes characters into vector strokes and checks them line by line - delivering an explainable, GMP grade legibility score without manual teach in. It handles complex scripts (e.g. Arabic, Chinese, Japanese) and touching characters (e.g., "VV", "Qj"), lets you tune sensitivity per area, and reduces false classifications for faster setup and better auditability.

Hardware in one station

A height-adjustable mount with alignment guides for fast centering, a matrix camera with matched illumination, an I/O interface for printer trigger and feed, and an industrial panel PC running QualiReader I. You supply your preferred printer with or without a rewinder, so the cell mirrors your current process without any unnecessary re-engineering.

Technical snapshot

- **Inspection methods:** LegibilityCheck (low/high sensitivity), OCR/OCV, code read & compare (grading approximation), pre-print/mix-up; maskable out-map areas.
- **Integration:** Level 3 XML interface, Hotfolder, optional database connections.
- **Operation:** touchscreen UI, order sheet via code scanner, or remote Level 3 control.
- **Data:** Orders & Articles with database storage; results local to IPC and optionally pushed to IT systems.

Why QualiVision?

- **28+ years of expertise** in machine vision and inspection systems
- **3'000+ systems installed** in the Pharma & Medtech industry
- **2'000+ machines running** in digital print inspection
- **Validated pharma-grade software:** CFR 21 Part 11 compliant offering Audit trail, access control, change management, 2nd signature
- **Entirely in-house software development:** No third-party dependencies → fast bug fixing & support
- **Forward compatibility guaranteed:** Easy upgrades to newer hardware or Windows versions
- **Swiss-made quality & precision**

QualiVision AG, Tödistrasse 50, CH – 8810 Horgen

☎ +41 43 500 55 00

✉ info@qualivision.ch

QualiVision GmbH, Rudolf-Diesel-Straße 24

DE – 64625 Bensheim

☎ +49 6151 460 52 50

